




C6.60 Hi-Tip (Gasoline)


01/06/2018

This page is intentionally left blank.


C6.60-BHE - C6.60 Hi-Tip (Gasoline).....	4
CRD.06.921.4 - Dashboard-frame.....	6
CRD.06.902.1 - Undercarriage.....	10
CRD.06.903.0 - Dashboard.....	12
CRD.06.924.0 - Engine Hood.....	14
CRD.06.925.0 - Engine / Pump Group.....	16
CRD.06.925.1 - Engine / Pump Group.....	18
CRD.06.906.0 - Transmission.....	20
CRD.06.906.1 - Transmission.....	22
CRD.06.907.2 - Wheels and Rollers.....	24
CRD.06.909.0 - Stacke-Body Hi-Tip.....	26
CRD.06.910.0 - Brake and Accelerator.....	30
CRD.06.910.1 - Brake and Accelerator.....	32
CRD.06.910.2 - Brake and Accelerator.....	34
CRD.06.931.0 - Impianto Idraulico.....	36
CRD.06.913.0 - Hydraulic System (Services).....	38
CRD.06.914.0 - Hydraulic System (Tank).....	42
CRD.06.935.0 - Electric System (Gasoline).....	44
CRD.06.935.1 - Electric System (Gasoline).....	46
CRD.06.935.2 - Electric System (Gasoline).....	48
Components index.....	50




Pos.	Description
Tav. 1	Dashboard-frame
Tav. 2	Undercarriage
Tav. 3	Dashboard
Tav. 4	Engine Hood
Tav. 5	Engine / Pump Group
Tav. 5	Engine / Pump Group
Tav. 6	Transmission
Tav. 6	Transmission
Tav. 7	Wheels and Rollers
Tav. 8	Stacke-Body Hi-Tip
Tav. 10	Brake and Accelerator
Tav. 10	Brake and Accelerator
Tav. 10	Brake and Accelerator
Tav. 11	Impianto Idraulico
Tav. 12	Hydraulic System (Services)
Tav. 14	Hydraulic System (Tank)
Tav. 15	Electric System (Gasoline)
Tav. 15	Electric System (Gasoline)
Tav. 15	Electric System (Gasoline)




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1a	C3030.40.03	1	Dashboard-Frame RI - AC	S60	Valido per versioni RI
	1b	C3030.40.01	1	Dashboard-Frame Hi-Tip	S60	Valido per versioni Hi-Tip
	2	C3000.27.00	1	Foot-Plate		
	3	C3000.27.04	1	Footboard blocker		
	4	C2023	2	Self-locking nut	M12	
	5	C2003	2	Flat washer	Ø12	
	6	C3000.27.05	1	Footboard support	L	
	7	C2073	2	Hex Head Cap Screw	M12x30	
	8	C2092	6	Flange nut	M8	
	9	C3000.27.01	1	Footboard support	R	
	10	C2075	6	Flange Hex Head Cap Screw	M8 x 20	
	11	C2064	11	Flange Hex Head Cap Screw	M6x20	
	12	C3010.04.02	1	Pre-filter cap		
	13	C3070.10.02	1	Battery cover		
	14	C1052.00.03	3	Knob	M6x25	
	15	C1184	2	Anti-vibration mount	Ø40 h20 M8	Replacement time: 0h 05m
	16a	C3030.19.02	2	Anti-Vibration support	RI	
	16b	C3030.19.03	2	Anti-Vibration support	AC	
	16c	C3030.19.04	2	Anti-Vibration support	HI	
	17	C2001	2	Flat washer	Ø8	
	18	C2085	2	Self-locking nut thin	M8	
	19	C3030.41.00	1	Safety device body dumper	60 hi-tip	Valido per versioni Hi-Tip
	20	C3030.41.02	1	Safety device body dumper	60 RI	Valido per versioni Hi-Tip
	20a	C3030.41.01	1	Safety device arm	60 hi-tip	Valido per versioni RI
	21a	C3000.25.00	1	Cover	S60	
	21b	C3000.25.01	1	Carterino AC	S60	
	22	C1047	2	Grease nipple	M6	
	23	C3000.19.10	1	Foot-Plate Kit	S60	
	24	C3000.17.14	1	Cover (L)		




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	25	C3000.17.15	1	Cover (R)		
	26	C2091.01.00	2	Flange Hex Head Cap Screw	M8x16	
	27	C0190.12.03	4	Flat Head Socket Cap Screw	M6x20	
	28	C2000.01.01	4	Flat washer	Ø6x24	
	29	C2030.01.00	6	Flange nut	M6	
	30	C3000.17.12	1	Cover (L)		
	31	C3000.17.13	1	Cover (R)		
	32	C2052.03.00	4	Flange Hex Head Cap Screw	M10x35	
	33	C3030.26.00	2	Stopper		
	34	C2019	4	Flange nut	M10	
	35	C2047	2	Hexagon Socket Head Cap Screw	M6x16	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3040.02.02	1	Frame	S60	
	2	C3000.26.00	1	Rear Protection		
	3	C2050.00.01	6	Hex Head Cap Screw	M10x16	
	4	C2012.00.10	12	Spacer washer	Ø10	
	5	C2030.01.00	2	Flange nut	M6	
	6	C2087	2	Flange Hex Head Cap Screw	M6x16	
	7	C2064	10	Flange Hex Head Cap Screw	M6x20	
	8	C3040.04.02	2	Slide		
	9	C2002	6	Flat washer	Ø10	
	10	C2022	8	Self-locking nut	M10	
	11	C7081.03.02	2	Cover		
	12	C2054.01.00	4	Hex Head Cap Screw	M10x110	
	13	C2052.01.00	4	Hex Head Cap Screw	M10x70	
	14	C0280.00.04	4	Shackle	7/16"	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3060.03.02	1	Plastic protection	S60	
	1	C3060.03.03	1	Plastic protection	S60 HiTip	
	1	C3060.03.04	1	Plastic protection	S60 HIAC	
	2	C3090.14.00	1	Dashboard Sticker		Valido per versioni RI
	2a	C3090.14.01	1	Dashboard Sticker	Hi-Tip	Valido per versioni Hi-Tip
	3	C3090.14.10	1	Dashboard Stickers Kit		Valido per versioni RI
	3a	C3090.14.11	1	Dashboard Stickers Kit	Hi-Tip	Valido per versioni Hi-Tip
	4	C1094.50.01	1	Safety Stickers	S60	
	5	C2064	6	Flange Hex Head Cap Screw	M6x20	
	6	C2063.11.02	10	Hexagon Socket Button Head Cap Screw	M6x20	
	7	C2000	10	Flat washer	Ø6	
	8	C1092.13.06	1	Handle	S60	
	8a	C1092.13.16	1	Handle with protection	S60	
	9	C0060.02.00	1	Documents holder	Ø55	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3060.00.01	1	Engine-hood	S60	
	1a	C3060.01.00	1	Engine-hood cpt Kit	S60	
	2	C3060.02.00	1	Insulation Kit	S60	
	3	C2021	4	Self-locking nut	M8	
	4	C2001	4	Flat washer	Ø8	
	5	C3060.08.06	2	Hinge		
	6	C2000	34	Flat washer	Ø6	
	7	C2063.11.02	11	Hexagon Socket Button Head Cap Screw	M6x20	
	8	C3060.05.00	1	Hood Frame	S60	
	9	C3060.08.10	1	Sealed Lever Latch	Locking	
	9	C3060.08.11	1	Spare Key	spare	
	10	C1094.20.10	1	Sticker		
	11	C2087	1	Flange Hex Head Cap Screw	M6x16	
	12	C3000.29.01	1	Mesh L	S60	
	13	C3000.28.10	1	Mesh Frame	S60b	
	14	C3000.28.02	1	Mesh Frame	S60	
	15	C3000.29.02	1	Mesh R	S60	
	16	C2030.01.00	21	Flange nut	M6	
	17	C3010.12.05	1	Mesh Frame		
	18	C3000.29.03	1	Upper mesh	S60	
	19	C2063.11.04	1	Hexagon Socket Button Head Cap Screw	M6x35	
	20	C1199	2	Cable holdfast		
	21	C3060.08.20	1	Hood Safety Cable		
	22	C0191.01.53	8	Cage nut	M6-3,5	
	23	C3000.29.04	1	Retina superiore dx	S60	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1109.00.10	1	Engine Honda GX270	Electric Start	
	2	C2082	4	Hex Head Cap Screw	M8×35	
	3	C2046	2	Hex Head Cap Screw	UNF 5/16x1-1/4	
	6	C2030.01.00	10	Flange nut	M6	
	13	C1092.16.04	1	Protection		
	15	C1254.00.03	1	Bell Housing		Replacement time: 1h 30m
	16	C2001	8	Flat washer	Ø8	
	17	C2088.01.00	4	Hexagon Socket Head Cap Screw	M8x25	
	18	C2021	4	Self-locking nut	M8	
	19	C2015.01.00	4	Flange Hex Head Cap Screw	M8x40	
	20	C1119	4	Anti-Vibration mount	Ø46 h22 68	Replacement time: 0h 15m
	21	C3120.04.00	1	Hydraulic Pump	3-1	Replacement time: 1h 00m
	22	C2000	4	Flat washer	Ø6	
	23	C2015.02.00	4	Hexagon Socket Head Cap Screw	M6x25	
	24	C1118.10.00	1	Braided copper ground		
	25	C3000.09.06	1	Motor Support		
	26	C2064	9	Flange Hex Head Cap Screw	M6x20	
	27	C3210.26.05	1	Muffler Insulation Cover	Honda GX270	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1109.00.10	1	Engine Honda GX270	Electric Start	
	2	C2082	4	Hex Head Cap Screw	M8x35	
	3	C0190.22.02	6	Hex Head Cap Screw	M6x16	
	4	C0189.01.02	1	Hexagonal blind rivet nut	M6	
	5	C0191.01.52	1	Cage nut	M6-2,5	
	6	C2030.01.00	11	Flange nut	M6	
	15	C1254.00.03	1	Bell Housing		Replacement time: 1h 30m
	16	C2001	8	Flat washer	Ø8	
	17	C2088.01.00	4	Hexagon Socket Head Cap Screw	M8x25	
	18	C2021	4	Self-locking nut	M8	
	19	C2015.01.00	4	Flange Hex Head Cap Screw	M8x40	
	20	C1119	4	Anti-Vibration mount	Ø46 h22 68	Replacement time: 0h 15m
	21	C3120.04.00	1	Hydraulic Pump	3-1	Replacement time: 1h 00m
	22	C2000	4	Flat washer	Ø6	
	23	C2015.02.00	4	Hexagon Socket Head Cap Screw	M6x25	
	24	C1118.10.00	1	Braided copper ground		
	25	C3000.09.06	1	Motor Support		
	26	C2064	9	Flange Hex Head Cap Screw	M6x20	
	27	C3000.28.11	1	Muffler Cover	S60b	
	27a	C3000.28.61	1	Muffler Insulation Cover	S60b	
	28	C3000.28.12	1	Cover Cap	S60b	
	28a	C3000.28.62	1	Cap Insulation Cover	S60b	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1074.00.14	2	Travel Motor	C6.60	
	1CKG	C1074.00.04.KG	2	Engine Gaskets Kit		
	2	C2023	8	Self-locking nut	M12	
	3	C2003	12	Flat washer	Ø12	
	4	C1023	1	Parallel Key	10x8x20	
	5	C2060	4	Hexagon Socket Head Cap Screw	M12x45	
	6	C3040.10.00	1	Drive Sprocket hub	S60	
	7	C3040.09.00	1	Drive Sprocket	S60	Replacement time: 0h 30m
	8	C2038	5	Flange Hex Head Cap Screw	M10x30	
	9	C3040.11.00	2	Rubber Track	180x60x47	Replacement time: 0h 15m
	10	C2012.00.02	2	Washer	M8x48x8	
	11	C2088	2	Flange Hex Head Cap Screw	M8x25	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1074.00.16	2	Travel Motor	C6.60	Replacing Time: 2h 30m
	1CKG	C1074.00.06.KG	2	Engine Gaskets Kit	C6.50 / C6.60	
	2	C2023	8	Self-locking nut	M12	
	3	C2003	12	Flat washer	Ø12	
	4	C1023	1	Parallel Key	10x8x20	
	5	C2060	4	Hexagon Socket Head Cap Screw	M12x45	
	6	C3040.10.00	1	Drive Sprocket hub	S60	
	7	C3040.09.00	1	Drive Sprocket	S60	Replacement time: 0h 30m
	8	C2038	5	Flange Hex Head Cap Screw	M10x30	
	9	C3040.11.00	2	Rubber Track	180x60x47	Replacement time: 0h 15m
	10	C2012.00.02	2	Washer	M8x48x8	
	11	C2088	2	Flange Hex Head Cap Screw	M8x25	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1a	C1036.05.03	4	Mudguard Wash	Ø65	
	1	C1036.01.00	16	Mudguard Wash		
	2	C1068	20	Ball Bearing		
	3	C1035.00.02	2	Tensioning Wheel		
	4	C1304.01.12	2	Nut for tensioner		
	5	C1304.01.11	2	Tensioner		
	6	C1304.01.02	2	Tensioning Wheel Support		
	7	C2027	4	Set Screw	M8x20	
	8	C1135	2	Axle Shaft	Ø20	
	9	C2025	10	Self-locking nut fine thread	M20	
	10	C2004	28	Flat washer	Ø20 ZN	
	11	C1036	8	Roller		Replacement time: 1h 00m
	12	C1046	8	Spacer		
	13	C2071.00.02	6	Pin w/greaser	M20x180	
	14	C1047	10	Grease nipple	M6	
	15	C3040.05.00	2	Operating lever		
	16	C1036.03.00	2	Spacer		
	17	C1035.03.04	8	Spacer	h=8	
	18	C2071.00.01	4	Pin w/greaser	M20x160	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1a	C3030.17.00	1	Skip	Hi-Tip 6.60	
	1b	C3030.17.03	1	Skip	6.60 HIAC	
	2	C2040.01.00	1	Flat Head Socket Cap Screw	M8×15	
	3	C3030.25.02	1	Gudgeon-Pin		
	4	C2085	7	Self-locking nut thin	M8	
	5	C3091.01.00	1	Stickers Kit	6.6	
	6	C3030.04.05	3	Gudgeon-Pin		
	7	C2025.00.01	5	Self-locking nut fine thread	M20	
	8	C2004	3	Flat washer	Ø20 ZN	
	9	C3030.03.07	1	Arm HiTip	S60	Replacement time: 1h 00m
	10	C3030.07.04	1	Gudgeon-Pin		
	11	C2091	5	Hex Head Cap Screw	M8×16	
	12	C3030.27.04	1	Gudgeon-Pin		
	13	C2041	2	Hex Head Cap Screw	M6x40	
	14	C2020	2	Self-locking nut	M6	
	15	C1047	3	Grease nipple	M6	
	16	C3030.05.05	1	Connecting Rod	S60	Replacement time: 0h 30m
	17	C2003	2	Flat washer	Ø12	
	18	C2049	4	Hex Head Cap Screw	M8x20	
	19	C3030.28.00	2	Piston Pin Bushing		
	20	C2073.01.00	2	Hex Head Cap Screw	M12x25	
	21	C2050.01.00	4	Hex Head Cap Screw	M10x25	
	22	C3030.21.00	1	Connection		
	23	C3030.02.04	2	Short Gudgeon-Pin		
	24	C2028.01.00	4	Hex Head Cap Screw	M14×30	
	25	C2003.01.00	4	Flat washer	Ø14 ZN	
	26	C3030.22.01	2	Connection		
	27	C3030.20.03	2	Connecting Rod		
	28	C3030.06.04	1	Connecting Rod Set		Replacement time: 1h 00m




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	29	C2004.00.01	2	Spacer washer	D20x58x8	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1259.01.00	1	Command lever		
	2	C3040.12.01	1	Cable Hose		Replacement time: 0h 30m
	3	C3040.12.02	1	Wire		
	4	C1198	3	Cable Hose Terminal		
	5	C1221	2	Adjusting Screw		
	6	C2030	2	Nut	M6	
	7	C3040.13.04	2	Gasket	GHK Ø20-28	
	8	C3040.13.02	2	Protection cup		
	9	C3040.13.08	2	Seeger Ring	Ø14x1 est DIN471	
	10	C3040.13.06	2	Spring		
	10a	C3040.12.00	1	Brake command kit		
	11	C3040.07.01	1	Long bolt of brake		
	12	C3040.07.00	1	Short bolt of brake		
	13	C3060.04.00	1	Bracket	S60	
	14	C2041.01.00	1	Flange Hex Head Cap Screw	M6x40	
	15	C3060.06.00	1	Brake support	S60	
	16	C1016.01.00	1	Throttle cable w/wire		
	17	C2064	2	Flange Hex Head Cap Screw	M6x20	
	18	C2030.01.00	4	Flange nut	M6	
	19	C1015.00.01	1	Accelerator Lever		Replacement time: 0h 30m
	20	C2092	3	Flange nut	M8	
	21	C2075	3	Flange Hex Head Cap Screw	M8 x 20	
	22	C2015	2	Pin TSPEI Zn	M6x25	
	23	C2000	1	Flat washer	Ø6	
	24	C2020	1	Self-locking nut	M6	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1259.01.00	1	Command lever		
	2	C3040.12.01	1	Cable Hose		Replacement time: 0h 30m
	3	C3040.12.02	1	Wire		
	4	C1198	3	Cable Hose Terminal		
	5	C1221	2	Adjusting Screw		
	6	C2030	2	Nut	M6	
	7	C3040.13.04	2	Gasket	GHK Ø20-28	
	8	C3040.13.02	2	Protection cup		
	9	C3040.13.08	2	Seeger Ring	Ø14x1 est DIN471	
	10	C3040.13.06	2	Spring		
	10a	C3040.12.00	1	Brake command kit		
	11	C3040.07.01	1	Long bolt of brake		
	12	C3040.07.00	1	Short bolt of brake		
	13	C3060.04.00	1	Bracket	S60	
	14	C2041.01.00	1	Flange Hex Head Cap Screw	M6x40	
	15	C3060.06.00	1	Brake support	S60	
	16	C3010.20.03	1	Throttle Cable CPT		
	17	C2064	2	Flange Hex Head Cap Screw	M6x20	
	18	C2030.01.00	4	Flange nut	M6	
	19	C2020	1	Self-locking nut	M6	
	20	C2092	3	Flange nut	M8	
	21	C2075	3	Flange Hex Head Cap Screw	M8 x 20	
	22	C2015	2	Pin TSPEI Zn	M6x25	
	23	C2000	1	Flat washer	Ø6	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1259.01.00	1	Command lever		
	2	C3040.12.01	1	Cable Hose		Replacement time: 0h 30m
	3	C3040.12.02	1	Wire		
	4	C1198	3	Cable Hose Terminal		
	5	C1221	2	Adjusting Screw		
	6	C2030	2	Nut	M6	
	7	C3040.13.04	2	Gasket	GHK Ø20-28	
	8	C3040.13.02	2	Protection cup		
	9	C3040.13.08	2	Seeger Ring	Ø14x1 est DIN471	
	10	C3040.13.06	2	Spring		
	10a	C3040.12.00	1	Brake command kit		
	11	C3040.07.11	1	Catenaccio lungo		
	12	C3040.07.00	1	Short bolt of brake		
	13	C3060.04.00	1	Bracket	S60	
	14	C2041.01.00	1	Flange Hex Head Cap Screw	M6x40	
	15	C3060.06.00	1	Brake support	S60	
	16	C3010.20.03	1	Throttle Cable CPT		
	17	C2064	2	Flange Hex Head Cap Screw	M6x20	
	18	C2030.01.00	4	Flange nut	M6	
	19	C2020	1	Self-locking nut	M6	
	20	C2092	3	Flange nut	M8	
	21	C2075	3	Flange Hex Head Cap Screw	M8 x 20	
	22	C2015	2	Pin TSPEI Zn	M6x25	
	23	C2000	1	Flat washer	Ø6	
	24	C1207.02.01	1	Barrel Nipple		




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3020.13.04	1	Radiator	3/8"	Replacement time: 1h 00m
	2	C0020.07.03	6	Banjo bolt	3/8"	
	3	C0020.05.03	15	Copper Gasket	3/8"	
	4	C3020.06.01	1	Hydraulic Tube	Eye 3/8" - F0° 1/2"	
	5	C3020.10.01	1	Hydraulic Tube	Eye 3/8" - F90° 3/8	
	6	C0020.01.03	2	Nipple	3/8" MM	
	7	C3020.10.02	1	Hydraulic Tube	F45° 3/8 - Eye 3/8"	
	8	C0020.06.06	1	Bonded Seal	3/4"	
	9	C0020.01.06	1	Nipple	3/4" MM	
	10	C1127.39.04	2	Clamp	Ø20-32	
	11	C1126.10.00	1	Connection	F90° 3/4"	
	12	C1130.09.00	1	Rubber hose	Ø18-26	
	13	C3020.07.01	1	Hydraulic Tube	F90° 3/8" - Eye 3/8"	Replacement time: 0h 30m
	14	C3020.10.03	1	Hydraulic Tube	Eye 3/8" - Eye 3/8"	
	15	C0020.06.04	2	Bonded Seal	1/2"	
	16	C0020.07.04	1	Banjo bolt	1/2"	
	17	C0020.01.03	1	Nipple	3/8" MM	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1468.01.04	1	Hydraulic Tube	F90° 1/8" - 1/4"	
	2	C1468.01.03	1	Hydraulic Tube	F90° 1/8" - 1/4"	
	3	C2091	8	Hex Head Cap Screw	M8×16	
	4	C0020.06.02	8	Bonded Seal	1/4"	
	5	C0020.01.02	2	Nipple	1/4" MM	
	6	C1400.01.00	8	Pipe Clamp		
	7	C0020.07.03	4	Banjo bolt	3/8"	
	8	C1155.00.04	16	Bonded Seal	3/8"	
	9	C1468.01.09	1	Hydraulic Tube	F90° 3/8" - 3/8"	Replacement time: 0h 30m
	10	C1468.01.07	1	Hydraulic Tube	F90° 3/8" - 3/8"	Replacement time: 0h 30m
	11	C0020.49.04	4	Connection	Eye 1/2" - G3/8"	
	12	C0020.01.03	4	Nipple	3/8" MM	
	13	C1232	4	Reduction	3/8" - 1/8"	
	14	C3220.02.00	1	5 Lever Distributor	Hi-Tip	
	15	C2031	9	Nut	M8	
	16	C2001	4	Flat washer	Ø8	
	17	C3060.04.01	2	Bracket	S60	
	18	C1120.00.02	5	Rubber Bellow	Ø10	
	19	C1189.06.07	2	Lever	170 mm Ø10	
	20	C1053.10.02	2	Knob	Ø10	
	21	C1053	3	Knob		
	22	C1189.06.06	1	Lever	160 mm Ø10	
	23	C1189.06.04	1	Lever	140 mm Ø10	
	24	C1189.06.02	1	Lever	120 mm Ø10	
	25	C3020.02.03	1	Hydraulic Cylinder	S60	Replacement time: 0h 15m
	CKG	C3020.02.03.KG	1	Gaskets Kit		
	25	C3020.02.13	1	Hydraulic Cylinder	S60 DHEAC-ACBHE	Replacement time: 0h 15m
	26	C3020.01.05	1	Hydraulic Cylinder Hi-Tip	S60 w/block	Replacement time: 0h 15m
	CKG	C3020.01.05.KG	1	Gaskets Kit		




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	27	C1460.01.01	1	Hydraulic Hose	Eye 1/4" - F90° 1/8"	
	28	C1460.02.01	1	Hydraulic Hose	Eye 1/4" - F90° 1/8"	
	29	C1193	2	Banjo bolt	BF 1/4"	
	30	C3020.43.00	1	Spacer		
	31	C2091.01.00	1	Flange Hex Head Cap Screw	M8x16	




Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C1097.00.03	1	Vented Dipstick	C6.60 RI	
	1a	C1097.00.04	1	Vented Dipstick	C6.60 Hi-Tip	
	2	C1127.39.04	2	Clamp	Ø20-32	
	3	C1650.01.07	1	Filter Ø132	1.1/4"	
	4	C0020.16.03	1	Female Stud Coupling	3/4" L=50	
	5	C0020.06.06	1	Bonded Seal	3/4"	
	6	C1155	1	Bonded Seal	1/2"	
	7	C2020	1	Self-locking nut	M6	
	8	C1130.11.00	1	Rubber hose	Ø25-35	
	9	C2092	2	Flange nut	M8	
	10	C0020.15.04	1	Nipple	1/2"	
	11	C0008.00.13	1	Support		
	12	C0008.00.14	1	Tank 3-1	S60	Replacement time: 0h 30m
	13	C0008.00.12	1	Cap Tank		
	14	C2064	18	Flange Hex Head Cap Screw	M6x20	
	15	C1400.01.00	2	Pipe Clamp		
	16	C1127.31.03	1	Rubber Clamp	25	
	17	C1650.01.06	1	Filter	1/2"	
	18	C1650.01.17	1	Connection L		
	19	C3050.02.00	1	Gasket		



Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3070.16.00	1	Electrical wiring cpt		
	2	C3070.16.11	1	Electrical wiring Honda		
	3	C1121.02.00	1	Buzzer		
	4	C6070.25.00	1	DC OUT socket		-
	5	C1127.80.02	1	Hour-Counter		Replacement time: 0h 15m
	6	C1143.02.00	2	Rivet	Ø4	
	7	C1127.44.02	1	Horn-Button		
	8b	C3020.24.05	1	Electric Fan	F17-12C003-1S WPC	
	8a	C3020.24.04	1	Electric Fan	F17-12C003-1B WPC	Replacement time: 1h 00m
	9	C2034.01.00	8	Self-drilling Screw	M4x19	
	11	C0190.52.03	2	Hexagon Socket Button Head Cap Screw	M6x16	
	10	C6070.01.00	1	Battery Cut-Off Switch		Replacement time: 0h 15m
	12	C2030.01.00	3	Flange nut	M6	
	13	C6070.01.01	1	Cable Battery Cut-Off Switch		
	14	C1197.02.00	1	Ground Cable		
	15	C3070.11.00	1	Battery		Replacement time: 0h 30m
	16	C1198.01.00	1	Isolation pad		
	17	C1196.02.00	1	Battery Cable		
	18	C2064	5	Flange Hex Head Cap Screw	M6x20	
	19	C4210.01.01	1	Bracket		
	20	C4070.05.00	1	Sensor		Replacement time: 0h 10m
	21	C1127.48.02	1	Horn	12V	Replacement time: 0h 10m
	22	C3070.16.12	1	Ignition Switch w/Key	Honda	Replacement time: 0h 30m
	23	C3020.25.00	1	Sensor	3/8"	Tempo di sostituzione: 20m



Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3070.16.00	1	Electrical wiring cpt		
	2	C3070.16.13	1	Electrical wiring Honda		
	3	C1121.02.00	1	Buzzer		
	4	C6070.25.00	1	DC OUT socket		-
	5	C1127.80.02	1	Hour-Counter		Replacement time: 0h 15m
	6	C1143.02.00	2	Rivet	Ø4	
	7	C1127.44.02	1	Horn-Button		
	8b	C3020.24.05	1	Electric Fan	F17-12C003-1S WPC	
	8a	C3020.24.04	1	Electric Fan	F17-12C003-1B WPC	Replacement time: 1h 00m
	9	C2034.01.00	8	Self-drilling Screw	M4x19	
	11	C0190.52.03	2	Hexagon Socket Button Head Cap Screw	M6x16	
	10	C6070.01.00	1	Battery Cut-Off Switch		Replacement time: 0h 15m
	12	C2030.01.00	3	Flange nut	M6	
	13	C6070.01.01	1	Cable Battery Cut-Off Switch		
	14	C1197.02.00	1	Ground Cable		
	15	C3070.11.00	1	Battery		Replacement time: 0h 30m
	16	C1198.01.00	1	Isolation pad		
	17	C1196.02.00	1	Battery Cable		
	18	C2064	5	Flange Hex Head Cap Screw	M6x20	
	19	C4210.01.01	1	Bracket		
	20	C4070.05.00	1	Sensor		Replacement time: 0h 10m
	21	C1127.48.02	1	Horn	12V	Replacement time: 0h 10m
	22	C4270.02.04	1	Ignition Switch w/Key	Honda	Replacement time: 0h 30m
	23	C3020.25.00	1	Sensor	3/8"	Tempo di sostituzione: 20m
	24	C4200.12.01	1	Relais support		
	25	C4270.02.02	1	Relays Group		



Purch.	Pos.	Code	Q.ty	Description	Specifications	Notes
	1	C3070.16.00	1	Electrical wiring cpt		
	2	C3070.16.13	1	Electrical wiring Honda		
	3	C1121.02.00	1	Buzzer		
	4	C6070.25.00	1	DC OUT socket		-
	5	C1127.80.02	1	Hour-Counter		Replacement time: 0h 15m
	6	C1143.02.00	2	Rivet	Ø4	
	7	C1127.44.02	1	Horn-Button		
	8b	C3020.24.05	1	Electric Fan	F17-12C003-1S WPC	
	8a	C3020.24.04	1	Electric Fan	F17-12C003-1B WPC	Replacement time: 1h 00m
	9	C2034.01.00	8	Self-drilling Screw	M4x19	
	11	C0190.52.03	2	Hexagon Socket Button Head Cap Screw	M6x16	
	10	C6070.01.00	1	Battery Cut-Off Switch		Replacement time: 0h 15m
	12	C2030.01.00	4	Flange nut	M6	
	13	C6070.01.01	1	Cable Battery Cut-Off Switch		
	14	C1197.02.00	1	Ground Cable		
	15	C3070.11.00	1	Battery		Replacement time: 0h 30m
	16	C1198.01.00	1	Isolation pad		
	17	C1196.02.00	1	Battery Cable		
	18	C2064	5	Flange Hex Head Cap Screw	M6x20	
	19	C4210.01.00	1	Support		
	20	C4070.05.00	1	Sensor		Replacement time: 0h 10m
	21	C1127.48.02	1	Horn	12V	Replacement time: 0h 10m
	22	C4270.02.04	1	Ignition Switch w/Key	Honda	Replacement time: 0h 30m
	23	C3020.25.00	1	Sensor	3/8"	Tempo di sostituzione: 20m
	24	C4200.12.01	1	Relais support		
	25	C4270.02.02	1	Relays Group		
	26	C0190.02.02	1	Hexagon Socket Head Cap Screw	M6x12	
	27	C0189.01.02	2	Hexagonal blind rivet nut	M6	

Code	Parts Table	Pos.	Q.ty
C0008.00.12	CRD.06.914.0	13	1
C0008.00.13	CRD.06.914.0	11	1
C0008.00.14	CRD.06.914.0	12	1
C0020.01.02	CRD.06.913.0	5	2
C0020.01.03	CRD.06.913.0	12	4
	CRD.06.931.0	6	2
	CRD.06.931.0	17	1
C0020.01.06	CRD.06.931.0	9	1
C0020.05.03	CRD.06.931.0	3	15
C0020.06.02	CRD.06.913.0	4	8
C0020.06.04	CRD.06.931.0	15	2
C0020.06.06	CRD.06.914.0	5	1
	CRD.06.931.0	8	1
C0020.07.03	CRD.06.913.0	7	4
	CRD.06.931.0	2	6
C0020.07.04	CRD.06.931.0	16	1
C0020.15.04	CRD.06.914.0	10	1
C0020.16.03	CRD.06.914.0	4	1
C0020.49.04	CRD.06.913.0	11	4
C0060.02.00	CRD.06.903.0	9	1
C0189.01.02	CRD.06.925.1	4	1
	CRD.06.935.2	27	2
C0190.02.02	CRD.06.935.2	26	1
C0190.12.03	CRD.06.921.4	27	4
C0190.22.02	CRD.06.925.1	3	6
C0190.52.03	CRD.06.935.0	11	2
	CRD.06.935.1	11	2
	CRD.06.935.2	11	2
C0191.01.52	CRD.06.925.1	5	1
C0191.01.53	CRD.06.924.0	22	8
C0280.00.04	CRD.06.902.1	14	4

Code	Parts Table	Pos.	Q.ty
C1015.00.01	CRD.06.910.0	19	1
C1016.01.00	CRD.06.910.0	16	1
C1023	CRD.06.906.0	4	1
	CRD.06.906.1	4	1
C1035.00.02	CRD.06.907.2	3	2
C1035.03.04	CRD.06.907.2	17	8
C1036	CRD.06.907.2	11	8
C1036.01.00	CRD.06.907.2	1	16
C1036.03.00	CRD.06.907.2	16	2
C1036.05.03	CRD.06.907.2	1a	4
C1046	CRD.06.907.2	12	8
C1047	CRD.06.907.2	14	10
	CRD.06.909.0	15	3
	CRD.06.921.4	22	2
C1052.00.03	CRD.06.921.4	14	3
C1053	CRD.06.913.0	21	3
C1053.10.02	CRD.06.913.0	20	2
C1068	CRD.06.907.2	2	20
C1074.00.04.KG	CRD.06.906.0	1CKG	2
C1074.00.06.KG	CRD.06.906.1	1CKG	2
C1074.00.14	CRD.06.906.0	1	2
C1074.00.16	CRD.06.906.1	1	2
C1092.13.06	CRD.06.903.0	8	1
C1092.13.16	CRD.06.903.0	8a	1
C1092.16.04	CRD.06.925.0	13	1
C1094.20.10	CRD.06.924.0	10	1
C1094.50.01	CRD.06.903.0	4	1
C1097.00.03	CRD.06.914.0	1	1
C1097.00.04	CRD.06.914.0	1a	1
C1109.00.10	CRD.06.925.0	1	1
	CRD.06.925.1	1	1

Code	Parts Table	Pos.	Q.ty
C1118.10.00	CRD.06.925.0	24	1
	CRD.06.925.1	24	1
C1119	CRD.06.925.0	20	4
	CRD.06.925.1	20	4
C1120.00.02	CRD.06.913.0	18	5
C1121.02.00	CRD.06.935.0	3	1
	CRD.06.935.1	3	1
	CRD.06.935.2	3	1
C1126.10.00	CRD.06.931.0	11	1
C1127.31.03	CRD.06.914.0	16	1
C1127.39.04	CRD.06.914.0	2	2
	CRD.06.931.0	10	2
C1127.44.02	CRD.06.935.0	7	1
	CRD.06.935.1	7	1
	CRD.06.935.2	7	1
C1127.48.02	CRD.06.935.0	21	1
	CRD.06.935.1	21	1
	CRD.06.935.2	21	1
C1127.80.02	CRD.06.935.0	5	1
	CRD.06.935.1	5	1
	CRD.06.935.2	5	1
C1130.09.00	CRD.06.931.0	12	1
C1130.11.00	CRD.06.914.0	8	1
C1135	CRD.06.907.2	8	2
C1143.02.00	CRD.06.935.0	6	2
	CRD.06.935.1	6	2
	CRD.06.935.2	6	2
C1155	CRD.06.914.0	6	1
C1155.00.04	CRD.06.913.0	8	16
C1184	CRD.06.921.4	15	2
C1189.06.02	CRD.06.913.0	24	1

Code	Parts Table	Pos.	Q.ty
C1189.06.04	CRD.06.913.0	23	1
C1189.06.06	CRD.06.913.0	22	1
C1189.06.07	CRD.06.913.0	19	2
C1193	CRD.06.913.0	29	2
C1196.02.00	CRD.06.935.0	17	1
	CRD.06.935.1	17	1
	CRD.06.935.2	17	1
C1197.02.00	CRD.06.935.0	14	1
	CRD.06.935.1	14	1
	CRD.06.935.2	14	1
C1198	CRD.06.910.0	4	3
	CRD.06.910.1	4	3
	CRD.06.910.2	4	3
C1198.01.00	CRD.06.935.0	16	1
	CRD.06.935.1	16	1
	CRD.06.935.2	16	1
C1199	CRD.06.924.0	20	2
C1207.02.01	CRD.06.910.2	24	1
C1221	CRD.06.910.0	5	2
	CRD.06.910.1	5	2
	CRD.06.910.2	5	2
C1232	CRD.06.913.0	13	4
C1254.00.03	CRD.06.925.0	15	1
	CRD.06.925.1	15	1
C1259.01.00	CRD.06.910.0	1	1
	CRD.06.910.1	1	1
	CRD.06.910.2	1	1
C1304.01.02	CRD.06.907.2	6	2
C1304.01.11	CRD.06.907.2	5	2
C1304.01.12	CRD.06.907.2	4	2
C1400.01.00	CRD.06.913.0	6	8

Code	Parts Table	Pos.	Q.ty
	CRD.06.914.0	15	2
C1460.01.01	CRD.06.913.0	27	1
C1460.02.01	CRD.06.913.0	28	1
C1468.01.03	CRD.06.913.0	2	1
C1468.01.04	CRD.06.913.0	1	1
C1468.01.07	CRD.06.913.0	10	1
C1468.01.09	CRD.06.913.0	9	1
C1650.01.06	CRD.06.914.0	17	1
C1650.01.07	CRD.06.914.0	3	1
C1650.01.17	CRD.06.914.0	18	1
C2000	CRD.06.903.0	7	10
	CRD.06.910.0	23	1
	CRD.06.910.1	23	1
	CRD.06.910.2	23	1
	CRD.06.924.0	6	34
	CRD.06.925.0	22	4
	CRD.06.925.1	22	4
C2000.01.01	CRD.06.921.4	28	4
C2001	CRD.06.913.0	16	4
	CRD.06.921.4	17	2
	CRD.06.924.0	4	4
	CRD.06.925.0	16	8
	CRD.06.925.1	16	8
C2002	CRD.06.902.1	9	6
C2003	CRD.06.906.0	3	12
	CRD.06.906.1	3	12
	CRD.06.909.0	17	2
	CRD.06.921.4	5	2
C2003.01.00	CRD.06.909.0	25	4
C2004	CRD.06.907.2	10	28
	CRD.06.909.0	8	3

Code	Parts Table	Pos.	Q.ty
C2004.00.01	CRD.06.909.0	29	2
C2012.00.02	CRD.06.906.0	10	2
	CRD.06.906.1	10	2
C2012.00.10	CRD.06.902.1	4	12
C2015	CRD.06.910.0	22	2
	CRD.06.910.1	22	2
	CRD.06.910.2	22	2
C2015.01.00	CRD.06.925.0	19	4
	CRD.06.925.1	19	4
C2015.02.00	CRD.06.925.0	23	4
	CRD.06.925.1	23	4
C2019	CRD.06.921.4	34	4
C2020	CRD.06.909.0	14	2
	CRD.06.910.0	24	1
	CRD.06.910.1	19	1
	CRD.06.910.2	19	1
	CRD.06.914.0	7	1
C2021	CRD.06.924.0	3	4
	CRD.06.925.0	18	4
	CRD.06.925.1	18	4
C2022	CRD.06.902.1	10	8
C2023	CRD.06.906.0	2	8
	CRD.06.906.1	2	8
	CRD.06.921.4	4	2
C2025	CRD.06.907.2	9	10
C2025.00.01	CRD.06.909.0	7	5
C2027	CRD.06.907.2	7	4
C2028.01.00	CRD.06.909.0	24	4
C2030	CRD.06.910.0	6	2
	CRD.06.910.1	6	2
	CRD.06.910.2	6	2

Code	Parts Table	Pos.	Q.ty
C2030.01.00	CRD.06.902.1	5	2
	CRD.06.910.0	18	4
	CRD.06.910.1	18	4
	CRD.06.910.2	18	4
	CRD.06.921.4	29	6
	CRD.06.924.0	16	21
	CRD.06.925.0	6	10
	CRD.06.925.1	6	11
	CRD.06.935.0	12	3
	CRD.06.935.1	12	3
	CRD.06.935.2	12	4
C2031	CRD.06.913.0	15	9
C2034.01.00	CRD.06.935.0	9	8
	CRD.06.935.1	9	8
	CRD.06.935.2	9	8
C2038	CRD.06.906.0	8	5
	CRD.06.906.1	8	5
C2040.01.00	CRD.06.909.0	2	1
C2041	CRD.06.909.0	13	2
C2041.01.00	CRD.06.910.0	14	1
	CRD.06.910.1	14	1
	CRD.06.910.2	14	1
C2046	CRD.06.925.0	3	2
C2047	CRD.06.921.4	35	2
C2049	CRD.06.909.0	18	4
C2050.00.01	CRD.06.902.1	3	6
C2050.01.00	CRD.06.909.0	21	4
C2052.01.00	CRD.06.902.1	13	4
C2052.03.00	CRD.06.921.4	32	4
C2054.01.00	CRD.06.902.1	12	4
C2060	CRD.06.906.0	5	4

Code	Parts Table	Pos.	Q.ty
	CRD.06.906.1	5	4
C2063.11.02	CRD.06.903.0	6	10
	CRD.06.924.0	7	11
C2063.11.04	CRD.06.924.0	19	1
C2064	CRD.06.902.1	7	10
	CRD.06.903.0	5	6
	CRD.06.910.0	17	2
	CRD.06.910.1	17	2
	CRD.06.910.2	17	2
	CRD.06.914.0	14	18
	CRD.06.921.4	11	11
	CRD.06.925.0	26	9
	CRD.06.925.1	26	9
	CRD.06.935.0	18	5
	CRD.06.935.1	18	5
	CRD.06.935.2	18	5
C2071.00.01	CRD.06.907.2	18	4
C2071.00.02	CRD.06.907.2	13	6
C2073	CRD.06.921.4	7	2
C2073.01.00	CRD.06.909.0	20	2
C2075	CRD.06.910.0	21	3
	CRD.06.910.1	21	3
	CRD.06.910.2	21	3
	CRD.06.921.4	10	6
C2082	CRD.06.925.0	2	4
	CRD.06.925.1	2	4
C2085	CRD.06.909.0	4	7
	CRD.06.921.4	18	2
C2087	CRD.06.902.1	6	2
	CRD.06.924.0	11	1
C2088	CRD.06.906.0	11	2

Code	Parts Table	Pos.	Q.ty
	CRD.06.906.1	11	2
C2088.01.00	CRD.06.925.0	17	4
	CRD.06.925.1	17	4
C2091	CRD.06.909.0	11	5
	CRD.06.913.0	3	8
C2091.01.00	CRD.06.913.0	31	1
	CRD.06.921.4	26	2
C2092	CRD.06.910.0	20	3
	CRD.06.910.1	20	3
	CRD.06.910.2	20	3
	CRD.06.914.0	9	2
	CRD.06.921.4	8	6
C3000.09.06	CRD.06.925.0	25	1
	CRD.06.925.1	25	1
C3000.17.12	CRD.06.921.4	30	1
C3000.17.13	CRD.06.921.4	31	1
C3000.17.14	CRD.06.921.4	24	1
C3000.17.15	CRD.06.921.4	25	1
C3000.19.10	CRD.06.921.4	23	1
C3000.25.00	CRD.06.921.4	21a	1
C3000.25.01	CRD.06.921.4	21b	1
C3000.26.00	CRD.06.902.1	2	1
C3000.27.00	CRD.06.921.4	2	1
C3000.27.01	CRD.06.921.4	9	1
C3000.27.04	CRD.06.921.4	3	1
C3000.27.05	CRD.06.921.4	6	1
C3000.28.02	CRD.06.924.0	14	1
C3000.28.10	CRD.06.924.0	13	1
C3000.28.11	CRD.06.925.1	27	1
C3000.28.12	CRD.06.925.1	28	1
C3000.28.61	CRD.06.925.1	27a	1

Code	Parts Table	Pos.	Q.ty
C3000.28.62	CRD.06.925.1	28a	1
C3000.29.01	CRD.06.924.0	12	1
C3000.29.02	CRD.06.924.0	15	1
C3000.29.03	CRD.06.924.0	18	1
C3000.29.04	CRD.06.924.0	23	1
C3010.04.02	CRD.06.921.4	12	1
C3010.12.05	CRD.06.924.0	17	1
C3010.20.03	CRD.06.910.1	16	1
	CRD.06.910.2	16	1
C3020.01.05	CRD.06.913.0	26	1
C3020.01.05.KG	CRD.06.913.0	CKG	1
C3020.02.03	CRD.06.913.0	25	1
C3020.02.03.KG	CRD.06.913.0	CKG	1
C3020.02.13	CRD.06.913.0	25	1
C3020.06.01	CRD.06.931.0	4	1
C3020.07.01	CRD.06.931.0	13	1
C3020.10.01	CRD.06.931.0	5	1
C3020.10.02	CRD.06.931.0	7	1
C3020.10.03	CRD.06.931.0	14	1
C3020.13.04	CRD.06.931.0	1	1
C3020.24.04	CRD.06.935.0	8a	1
	CRD.06.935.1	8a	1
	CRD.06.935.2	8a	1
C3020.24.05	CRD.06.935.0	8b	1
	CRD.06.935.1	8b	1
	CRD.06.935.2	8b	1
C3020.25.00	CRD.06.935.0	23	1
	CRD.06.935.1	23	1
	CRD.06.935.2	23	1
C3020.43.00	CRD.06.913.0	30	1
C3030.02.04	CRD.06.909.0	23	2

Code	Parts Table	Pos.	Q.ty
C3030.03.07	CRD.06.909.0	9	1
C3030.04.05	CRD.06.909.0	6	3
C3030.05.05	CRD.06.909.0	16	1
C3030.06.04	CRD.06.909.0	28	1
C3030.07.04	CRD.06.909.0	10	1
C3030.17.00	CRD.06.909.0	1a	1
C3030.17.03	CRD.06.909.0	1b	1
C3030.19.02	CRD.06.921.4	16a	2
C3030.19.03	CRD.06.921.4	16b	2
C3030.19.04	CRD.06.921.4	16c	2
C3030.20.03	CRD.06.909.0	27	2
C3030.21.00	CRD.06.909.0	22	1
C3030.22.01	CRD.06.909.0	26	2
C3030.25.02	CRD.06.909.0	3	1
C3030.26.00	CRD.06.921.4	33	2
C3030.27.04	CRD.06.909.0	12	1
C3030.28.00	CRD.06.909.0	19	2
C3030.40.01	CRD.06.921.4	1b	1
C3030.40.03	CRD.06.921.4	1a	1
C3030.41.00	CRD.06.921.4	19	1
C3030.41.01	CRD.06.921.4	20a	1
C3030.41.02	CRD.06.921.4	20	1
C3040.02.02	CRD.06.902.1	1	1
C3040.04.02	CRD.06.902.1	8	2
C3040.05.00	CRD.06.907.2	15	2
C3040.07.00	CRD.06.910.0	12	1
	CRD.06.910.1	12	1
	CRD.06.910.2	12	1
C3040.07.01	CRD.06.910.0	11	1
	CRD.06.910.1	11	1
C3040.07.11	CRD.06.910.2	11	1

Code	Parts Table	Pos.	Q.ty
C3040.09.00	CRD.06.906.0	7	1
	CRD.06.906.1	7	1
C3040.10.00	CRD.06.906.0	6	1
	CRD.06.906.1	6	1
C3040.11.00	CRD.06.906.0	9	2
	CRD.06.906.1	9	2
C3040.12.00	CRD.06.910.0	10a	1
	CRD.06.910.1	10a	1
	CRD.06.910.2	10a	1
C3040.12.01	CRD.06.910.0	2	1
	CRD.06.910.1	2	1
	CRD.06.910.2	2	1
C3040.12.02	CRD.06.910.0	3	1
	CRD.06.910.1	3	1
	CRD.06.910.2	3	1
C3040.13.02	CRD.06.910.0	8	2
	CRD.06.910.1	8	2
	CRD.06.910.2	8	2
C3040.13.04	CRD.06.910.0	7	2
	CRD.06.910.1	7	2
	CRD.06.910.2	7	2
C3040.13.06	CRD.06.910.0	10	2
	CRD.06.910.1	10	2
	CRD.06.910.2	10	2
C3040.13.08	CRD.06.910.0	9	2
	CRD.06.910.1	9	2
	CRD.06.910.2	9	2
C3050.02.00	CRD.06.914.0	19	1
C3060.00.01	CRD.06.924.0	1	1
C3060.01.00	CRD.06.924.0	1a	1
C3060.02.00	CRD.06.924.0	2	1

Code	Parts Table	Pos.	Q.ty
C3060.03.02	CRD.06.903.0	1	1
C3060.03.03	CRD.06.903.0	1	1
C3060.03.04	CRD.06.903.0	1	1
C3060.04.00	CRD.06.910.0	13	1
	CRD.06.910.1	13	1
	CRD.06.910.2	13	1
C3060.04.01	CRD.06.913.0	17	2
C3060.05.00	CRD.06.924.0	8	1
C3060.06.00	CRD.06.910.0	15	1
	CRD.06.910.1	15	1
	CRD.06.910.2	15	1
C3060.08.06	CRD.06.924.0	5	2
C3060.08.10	CRD.06.924.0	9	1
C3060.08.11	CRD.06.924.0	9	1
C3060.08.20	CRD.06.924.0	21	1
C3070.10.02	CRD.06.921.4	13	1
C3070.11.00	CRD.06.935.0	15	1
	CRD.06.935.1	15	1
	CRD.06.935.2	15	1
C3070.16.00	CRD.06.935.0	1	1
	CRD.06.935.1	1	1
	CRD.06.935.2	1	1
C3070.16.11	CRD.06.935.0	2	1
C3070.16.12	CRD.06.935.0	22	1
C3070.16.13	CRD.06.935.1	2	1
	CRD.06.935.2	2	1
C3090.14.00	CRD.06.903.0	2	1
C3090.14.01	CRD.06.903.0	2a	1
C3090.14.10	CRD.06.903.0	3	1
C3090.14.11	CRD.06.903.0	3a	1
C3091.01.00	CRD.06.909.0	5	1

Code	Parts Table	Pos.	Q.ty
C3120.04.00	CRD.06.925.0	21	1
	CRD.06.925.1	21	1
C3210.26.05	CRD.06.925.0	27	1
C3220.02.00	CRD.06.913.0	14	1
C4070.05.00	CRD.06.935.0	20	1
	CRD.06.935.1	20	1
	CRD.06.935.2	20	1
C4200.12.01	CRD.06.935.1	24	1
	CRD.06.935.2	24	1
C4210.01.00	CRD.06.935.2	19	1
C4210.01.01	CRD.06.935.0	19	1
	CRD.06.935.1	19	1
C4270.02.02	CRD.06.935.1	25	1
	CRD.06.935.2	25	1
C4270.02.04	CRD.06.935.1	22	1
	CRD.06.935.2	22	1
C6070.01.00	CRD.06.935.0	10	1
	CRD.06.935.1	10	1
	CRD.06.935.2	10	1
C6070.01.01	CRD.06.935.0	13	1
	CRD.06.935.1	13	1
	CRD.06.935.2	13	1
C6070.25.00	CRD.06.935.0	4	1
	CRD.06.935.1	4	1
	CRD.06.935.2	4	1
C7081.03.02	CRD.06.902.1	11	2